

THROUGH THE LID ANTENNA (TTL-A)

FEATURES

Applications: For use in metal pit or vault installations where a standard 1-3/4" or 1-7/8" hole exists. The Mueller TTL-A provides a standardized method of installation and provides optimization of radio transmission out of the pits or vaults equipped with metal lids. The TTL-A provides a simple method of mounting current Mueller Mi.NET radio modules in an easily accessed installation location under the pit lid without additional hardware or tools.

Compliance: The TTL-A is compliant with the American Disabilities Act Section 4.5 and AASHTO H-20 Heavy Duty.

Construction: The TTL-A consists of three basic parts: TTL-A body, threaded nut, and a rubber washer. The design is made from both aluminum and polymer for optimum weight to strength ratio and minimal environmental impact.

Installation: The TTL-A threads into the top case of the Mi.NET Radio Module. Simply remove the Mi.NET module antenna cover by turning it counter clockwise and insert the TTL-A screwing it clockwise into the Mi.NET module after insertion through the lid. This permits the Radio Module to hang from the pit lid, optimizing the accessibility and performance of the device.

Maintenance: The Mueller Systems TTL-A is designed and manufactured to provide long service life with no maintenance required. In the event the exposed portion of the TTL-A is damaged, the entire assembly can be replaced quickly and easily in the field with no additional tools required.





THROUGH THE LID ANTENNA (TTL-A)


Materials and Specifications:

- MODEL NUMBER MS-TTL-A
- COMPATIBILITY Pit lids up to 2" thick

All Mi.NET Radio Versions with Threaded Top Housing

(The TTL-A is not compatible with Mi.Net modules manufactured prior to June 15th, 2019)

- CONNECTION Threaded connection to Mi.NET Radios via a 1-½-6 UNC Thread
- MATERIALS TTL-A Body Aluminum/Thermoplastic; Threaded Nut - Thermoplastic; Rubber Washer - Buna-N
- TEMPERATURE RANGE Operating Temperature: -40°F to + 158°F (-40°C to + 70°C); Humidity: 0% 100% condensing



For more information about Mueller or to view our full line of water products, please visit muellersystems.com or call Mueller customer service at 1.800.423.1323.

Mueller refers to one or more of Mueller Water Products, Inc. a Delaware corporation ("MWP"), and its subsidiaries. MWP and each of its subsidiaries are legally separate and independent entities when providing products and services. MWP does not provide products or services to third parties. MWP and each of its subsidiaries are liable only for their own acts and omissions and not those of each other. MWP brands include Mueller*, Echologics*, Hydro-Guard*, HyMAX*, Jones*, Krausz*, Mi.Net*, Milliken*, Pratt*, Pratt Industrial*, Singer*, and U.S. Pipe Valve & Hydrant. Please see muellerwp.com/brands and krauszusa.com

© 2020 Mueller Systems, LLC. All Rights Reserved. The trademarks, logos and service marks displayed in this document are the property of Mueller Water Products, Inc., its affiliates or other third parties. Products above marked with a section symbol (§) are subject to patents or patent applications. For details, visit www.mwppat.com. These products are intended for use in potable water applications. Please contact your Mueller Sales or Customer Service Representative concerning any other application(§).

